

# SA-ISO

---



PIM-Guard®, PIM-free, isolator snaps in between hanger and mounting surface, and between stacked hangers to remove metal to metal contact

## Product Classification

<b>Product Type</b>	Adapter
<b>Product Brand</b>	PIM-Guard®
<b>Ordering Note</b>	ANDREW® standard product (Global)

## General Specifications

<b>Accessories</b>	Adapters
<b>Color</b>	Black
<b>Hanger Type</b>	Snap-in hanger
<b>Mounting</b>	3/4 in drilled cable ladder   3/4 in through hole

## Dimensions

<b>Height</b>	26.9 mm   1.059 in
<b>Width</b>	43.94 mm   1.73 in
<b>Length</b>	3.56 mm   0.14 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

## Mechanical Specifications

<b>Maximum Loading</b>	Double stack for hangers SSH-M, SSH-L, SSH-XL   Double stack, 1-5/8 in cable   Triple stack, 1/2 in cable
<b>Vibration Survival</b>	≥4 hours at resonant frequency

# SA-ISO

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Height, packed</b>	17 cm   6.693 in
<b>Width, packed</b>	13 cm   5.118 in
<b>Length, packed</b>	10 cm   3.937 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.15 kg   0.331 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

