SF-DPM2-126



Co-location Dual Pipe Mount Kit; includes (2) 2-3/8 in OD x 126 in pipes

Product Classification		
Product Type	Co-location dual pipe mount kit	
General Specifications		
Mounting	Angle 60°, 203.2 mm (8 in) Angle 90°, 152.4 mm (6 in) Straight or tapered legs up to 203.2 mm (8 in) OD	
Note	Two 72 in x 8 in panel antenna per sector	
Pipe, quantity	2	
Tower Taper	Non-tapered Tapered	
Dimensions		
Height	3,200.4 mm 126 in	
Face Width	1.463 m 4.8 ft	
Width	1,447.8 mm 57 in	
Length	0.396 m 1.3 ft	
Pipe Length	3,200.4 mm 126 in	
Face Support Pipe Diameter	88.9 mm 3.5 in	
Mounting Diameter, maximum	203.2 mm 8 in	
Mounting Diameter, minimum	0 mm 0 in	
Pipe Outer Diameter	60.96 mm 2.4 in	
Stand-off Distance	391.16 mm 15.4 in	
Material Specifications		
Material Type	Hot dip galvanized steel	
Mechanical Specifications		

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: March 23, 2023



SF-DPM2-126

Wind Rating120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBCWind Rating Test MethodTIA/EIA-222

Packaging and Weights

Included	Clamps Frame Pipe mounts Pipes Saddle mounts
Packaging quantity	1
Weight, net	130.5 kg 287.703 lb

Regulatory Compliance/Certifications

Agency Cla	ssification
------------	-------------

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: March 23, 2023

