

PROPEL-CABLED-MODULES

Base Product



Pre-terminated Propel Cabled Modules available in all module sizes and fiber counts up to 288 fibers

- Pre-cabled modules on End A reduces signal loss
- Pre-cabled modules can be installed from rear of panel
- Serialized QR code provides easy access to factory optical test results

Propel Cabled Modules provide a pre-terminated solution for simplified and efficient installation. They are available in all of the Propel module sizes on End A and End B can be another Propel module, MPO or stub.

Cable fiber counts range from 8 fibers – 288 fibers and cable lengths from 1 meter – 400 meters. Short cable lengths within rack can use patch cord cable for easy routing within the rack and longer lengths use ruggedized trunk cable.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cabled module
Product Brand	Propel
Product Series	PPL

General Specifications

Interface, front	LC/UPC SN/UPC
Interface, rear	LC/UPC MPO SN/UPC Stub

Optical Specifications

Fiber Mode	Multimode Singlemode
Fiber Type	OM4 OM5 OS2

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	c-UL-us