# FD3-AB096J00JKBP1



Enhanced Mini FDH, 96F loaded pole/wall mounted cabinet, SC/APC, PNP splitter capable, Dielectric Loose Tube Cable, 100ft stubs using a 1x96F distribution cable assembly and a 1x12F feeder

#### Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
General Specifications	
Access	Front
Cable Type	Dry Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	96
Fibers per Distribution Cable, quantity	96
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole   Wall
Splitter Slots, quantity	8
Dimensions	
Height	584.2 mm   23 in
Width	330.2 mm   13 in
Depth	203.2 mm   8 in
Cable Length	30.48 m   100 ft
Enclosure Size	Mini
Material Specifications	
Finish	Powder coated

Material Type

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 10, 2024

Aluminum



# FD3-AB096J00JKBP1

### **Environmental Specifications**

Environmental Space

**Qualification Standards** 

Above ground | Aerial Telcordia GR-3123-CORE | Telcordia GR-3125-CORE

#### Packaging and Weights

Packaging quantity

Packaging Type

Pallet

1

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted





©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 10, 2024

