

# MP-PP15M-B

---



PIM Optimized Adjustable Monopole Platform Base Kit with 15ft Face - 2-7/8in OD Face Pipes & Top Rail -No Antenna Pipes Included

## Product Classification

<b>Product Type</b>	Co-location platform
<b>Product Brand</b>	PIM-guard

## General Specifications

<b>Mounting</b>	Monopole, 304.8–1143 mm (12–45 in) OD
<b>Pipe, quantity</b>	0
<b>Sectors, quantity</b>	3

## Dimensions

<b>Face Width</b>	4.572 m   15 ft
<b>Width</b>	4,572 mm   180 in
<b>Face Support Pipe Diameter</b>	73.152 mm   2.88 in
<b>Mounting Diameter, maximum</b>	1,143 mm   45 in
<b>Mounting Diameter, minimum</b>	304.8 mm   12 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating Test Method</b>	TIA/EIA-222
--------------------------------	-------------

## Packaging and Weights

<b>Included</b>	Platform   Rail   Ring mount
<b>Packaging quantity</b>	1

# MP-PP15M-B

---

**Weight, net**

934.718 kg | 2,060.7 lb