


RVVS4-65S-R3



14-port sector antenna, 2x 698-960(R1), 4x 1695-2690(Y1&Y2) MHz, 65° HPBW and 8x 3300-3800(P1) MHz, 90° HPBW, 4x RET.

- All Internal RET actuators are connected in “Cascaded SRET” configuration
- M-LOC cluster connector for 3.3-3.8GHz, equipped with calibration port
- Combination of FDD MIMO antenna and 3.5GHz 8T8R TDD beam forming antenna, all in one for 5G ready

General Specifications

Antenna Type	Sector- and beamforming
Band	Multiband
Calibration Connector Interface	M-LOC
Calibration Connector Quantity	1
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female M-LOC
RF Connector Location	Bottom
RF Connector Quantity, high band	8
RF Connector Quantity, mid band	4
RF Connector Quantity, low band	2
RF Connector Quantity, total	14

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10–30 Vdc
Internal RET	High band (1) Mid band (2)
Power Consumption, active state, maximum	10 W

RVVS4-65S-R3

Power Consumption, idle state, maximum	2 W
Protocol	3GPP/AISG 2.0

Dimensions

Width	395 mm 15.551 in
Depth	228 mm 8.976 in
Length	800 mm 31.496 in
Net Weight, antenna only	16.6 kg 36.597 lb

Array Layout




Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	698-960	1-2	NA	NA
Y1	1695-2690	3-4	1	CPxxxxxxxxxxxxxxxxY1
Y2	1695-2690	5-6	2	CPxxxxxxxxxxxxxxxxY2
P1	3300-3800	7-14	3	CPxxxxxxxxxxxxxxxxP1

Left Right
Bottom

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration

RVVS4-65S-R3



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 3300 – 3800 MHz 698 – 960 MHz
Polarization	±45°
Total Input Power, maximum	800 W @ 50 °C

Electrical Specifications

	R1	R1	Y1,Y2	Y1,Y2	Y1,Y2
Frequency Band, MHz	698–862	880–960	1695–1920	1920–2200	2300–2690
RF Port	1,2	1,2	3-6	3-6	3-6
Beamwidth, Horizontal, degrees	70	68	70	71	63
Beamwidth, Vertical, degrees	27.7	22.8	13.2	12	10.3
Beam Tilt, degrees	12	12	2–12	2–12	2–12
USLS (First Lobe), dB	14	13	16	15	15
Front-to-Back Ratio at 180°, dB	32	33	33	34	31
Front-to-Back Total Power at 180° ± 30°, dB	21	22	26	28	27
CPR at Boresight, dB	20	23	22	24	19
CPR at Sector, dB	10	10	15	11	8

RVVS4-65S-R3

Isolation, Cross Polarization, dB	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	200	200	200	200	150

Electrical Specifications, BASTA

Frequency Band, MHz	698–862	880–960	1695–1920	1920–2200	2300–2690
Gain by all Beam Tilts, average, dBi	11.5	11.7	14.1	14.3	15
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.4	±0.5	±0.5	±0.6
Beamwidth, Horizontal Tolerance, degrees	±2.2	±2.3	±4.4	±4.6	±6.6
Beamwidth, Vertical Tolerance, degrees	±3.3	±2.1	±0.9	±0.9	±0.8
USLS, beampeak to 20° above beampeak, dB			16	15	15

Electrical Specifications

	P1	P1
Frequency Band, MHz	3300–3600	3600–3800
RF Port	7-14	7-14
Beamwidth, Horizontal, degrees	81	74
Beamwidth, Vertical, degrees	7.2	6.8
Beam Tilt, degrees	0–10	0–10
USLS (First Lobe), dB	15	14
Front-to-Back Ratio at 180°, dB	29	29
Front-to-Back Total Power at 180° ± 30°, dB	20	22
Coupling level, Amp, Antenna port to Cal port, dB	-26	-26
Coupling level, max Amp Δ, Antenna port to Cal port, dB	±2	±2
Coupler, max Amp Δ, Antenna port to Cal port, dB	0.9	0.9

RVVS4-65S-R3

Coupler, max Phase Δ , Antenna port to Cal port, degrees	7	7
CPR at Boresight, dB	14	15
CPR at Sector, dB	7	6
Isolation, Cross Polarization, dB	25	25
Isolation, Inter-band, dB	25	25
Isolation, Co-polarization, dB	20	20
VSWR Return loss, dB	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-140	-140
Input Power per Port at 50°C, maximum, watts	75	75

Electrical Specifications, BASTA

Frequency Band, MHz	3300–3600	3600–3800
Gain by all Beam Tilts, average, dBi	14.3	14.7
Gain by all Beam Tilts Tolerance, dB	±1.4	±1.2
Beamwidth, Horizontal Tolerance, degrees	±31.8	±20.3
Beamwidth, Vertical Tolerance, degrees	±0.9	±0.8
USLS, beampeak to 20° above beampeak, dB	14	12

Electrical Specifications, Broadcast 65°

Frequency Band, MHz	3300–3600	3600–3800
Gain, dBi	17.6	17.8
Beamwidth, Horizontal, degrees	65	65
Beamwidth, Vertical, degrees	7.1	6.6
Front-to-Back Total Power at 180° ± 30°, dB	26	28
USLS (First Lobe), dB	19	17

Electrical Specifications, Envelope Pattern

Frequency Band, MHz	3300–3600	3600–3800
Gain, dBi	19.5	19.7

RVVS4-65S-R3

Beamwidth, Horizontal at 10 dB, degrees	119	111
Front-to-Back Total Power at 180° ± 30°, dB	26	28
USLS (First Lobe), dB	19	19

Electrical Specifications, Service Beam

Frequency Band, MHz	3300–3600	3600–3800
Steered 0° Gain, dBi	19.5	19.7
Steered 0° Beamwidth, Horizontal, degrees	24	22
Steered 0° Front-to-Back Total Power at 180° ± 30°, dB	29	30
Steered 0° Horizontal Sidelobe, dB	13	13
Steered 30° Gain, dBi	18.2	18.9
Steered 30° Beamwidth, Horizontal, degrees	29	26
Steered 30° Front-to-Back Total Power at 180° ± 30°, dB	27	28

Mechanical Specifications

Wind Loading @ Velocity, frontal	110.0 N @ 150 km/h (24.7 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	93.0 N @ 150 km/h (20.9 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	220.0 N @ 150 km/h (49.5 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	126.0 N @ 150 km/h (28.3 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	509 mm 20.039 in
Depth, packed	386 mm 15.197 in
Length, packed	941 mm 37.047 in
Weight, gross	26.1 kg 57.541 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

RVVS4-65S-R3



Included Products

- BSAMNT-3 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance