

# RT-NF11-3-120

---



PIM-Guard High Capacity Non-Penetrating Roof Frame with Optimized Antenna Spacing 11 ft face, three 2-7/8 in OD x 120 in pipes

## Product Classification

<b>Product Type</b>	Non-penetrating roof frame
<b>Product Brand</b>	PIM-guard

## General Specifications

<b>Mounting</b>	Non-penetrating
<b>Pipe, quantity</b>	3

## Dimensions

<b>Height</b>	3,048 mm   120 in
<b>Face Width</b>	3.353 m   11 ft
<b>Width</b>	3,352.8 mm   132 in
<b>Length</b>	2.377 m   7.8 ft
<b>Pipe Length</b>	3,048 mm   120 in
<b>Face Support Pipe Diameter</b>	73.152 mm   2.88 in
<b>Pipe Outer Diameter</b>	73.152 mm   2.88 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact your local ANDREW representative
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

<b>Included</b>	Ballast tray   Frame   Plain end pipes (3)
<b>Packaging quantity</b>	1
<b>Weight, net</b>	484.6 kg   1,068.359 lb

# RT-NF11-3-120

---

## \* Footnotes

**Wind Rating**                    BWS—Base Wind Speed; FBC—Florida Building Code