


MP-PP15M-15C-126



PIM Optimized Adjustable Monopole Platform with 15ft Face - 2-7/8in OD Face Pipes & Top Rail - Includes (15) 2-7/8in OD x 126in Antenna Pipes

Product Classification

Product Type Co-location platform

General Specifications

Mounting Monopole, 304.8–1143 mm (12–45 in) OD

Pipe, quantity 15

Sectors, quantity 3

Dimensions

Height 3,200.4 mm | 126 in

Face Width 4.572 m | 15 ft

Width 4,572 mm | 180 in

Pipe Length 3,200.4 mm | 126 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Mounting Diameter, maximum 1,143 mm | 45 in

Mounting Diameter, minimum 304.8 mm | 12 in

Pipe Outer Diameter 73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

MP-PP15M-15C-126

Included	Plain end pipes Platform Rail Ring mount
Packaging quantity	1
Weight, net	1,463.969 kg 3,227.5 lb