



Fiber OSP cable, LightScope ZWP® Blown Single Jacket All-Dielectric Outdoor Central Tube Construction, 4 fiber, Singlemode G.657.A2, Gel-filled, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	Europe
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	B-CN


## General Specifications

<b>Cable Type</b>	Central tube, all dielectric   Microcable
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	0
<b>Inner Jacket Color</b>	White
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE BLW 810010283/DB 4 x G657A2 SM HDPE [SERIAL NUMBER] [METER MARK]
<b>Subunit, quantity</b>	1
<b>Fibers per Subunit, quantity</b>	4
<b>Total Fiber Count</b>	4

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	3 mm   0.118 in
<b>Diameter Over Jacket</b>	3.9 mm   0.154 in

## Representative Image



## Material Specifications

**Jacket Material** High density polyethylene (HDPE)

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	47 mm   1.85 in
<b>Minimum Bend Radius, storage coils</b>	47 mm   1.85 in
<b>Minimum Bend Radius, unloaded</b>	47 mm   1.85 in
<b>Tensile Load, long term, maximum</b>	70 N   15.737 lbf
<b>Compression</b>	10 N/mm   57.101 lb/in
<b>Compression Test Method</b>	IEC 60794-1-21 E3
<b>Flex</b>	25 cycles
<b>Impact</b>	2 N-m   17.701 in lb
<b>Impact Test Method</b>	IEC 60794-1-21 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1-21 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	IEC 60794-1-21 E7

## Optical Specifications

# 810010283/DB | B-004-CN-8G-M04BK/30G

---

**Fiber Type** G.657.A2

## Environmental Specifications

**Installation temperature** -10 °C to +60 °C (+14 °F to +140 °F)  
**Operating Temperature** -20 °C to +60 °C (-4 °F to +140 °F)  
**Storage Temperature** -20 °C to +60 °C (-4 °F to +140 °F)  
**Cable Qualification Standards** IEC 60794-1-2 | IEC 60794-5-10  
**Environmental Space** Air-blown, microduct  
**Jacket UV Resistance** UV stabilized  
**Water Penetration** 24 h  
**Water Penetration Test Method** IEC 60794-1 F5

## Environmental Test Specifications

**Low High Bend Test Method** IEC 60794-1-21 E11  
**Temperature Cycle** -20 °C to +60 °C (-4 °F to +140 °F)  
**Temperature Cycle Test Method** IEC 60794-1-22 F1

## Packaging and Weights

**Cable weight** 8.9 kg/km | 5.981 lb/kft

## Included Products

CS-8G-LT – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable