


MC-RM1550-3D



Dual Universal Ring Mount, 15 in to 50 in OD (Kit of 2 MC-RM1550-3)

Product Classification

Product Type Universal ring mount

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

Mounting Circumference, maximum 3,990.34 mm | 157.1 in

Mounting Circumference, minimum 1,196.34 mm | 47.1 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Ring mounts (2) | Threaded rod

Packaging quantity 2

Weight, net 235.868 kg | 520 lb