

# ATSBT-TOP-FM-5G | D85E01P86



## Top Smart Bias Tee 600-4200 MHz

- Reduces cable and site lease costs by eliminating the need for AISG home run cables
- Weatherproof AISG connectors
- Intuitive schematics simplify and ensure proper installation
- Enhanced lightning protection plus grounding stud for additional surge protection
- 4.3-10 female connector (BTS)
- 4.3-10 male connector (ANT)
- Operates at 10-30 Vdc
- AISG 1.1 and 2.0 compliant

## Product Classification

**Product Type** RET bias tee

## General Specifications

**AISG Input Connector** 8-pin DIN Female

**Antenna Interface** 4.3-10 Male

**Antenna Interface Signal** RF | dc Blocked

**BTS Interface** 4.3-10 Female

**BTS Interface Signal** AISG data | RF | dc

**Color** Silver

**EU Certification** CE

**Grounding Lug Thread Size** M6

**Smart Bias Tee Type** 10-30 V Top

## Dimensions

**Height** 68 mm | 2.677 in

**Width** 98 mm | 3.858 in

**Depth** 60 mm | 2.362 in

## Electrical Specifications

**3rd Order IMD** -161 dBc

**3rd Order IMD Test Method** Two +43 dBm CW Tones

**Insertion Loss, typical** 0.1 dB

**Electromagnetic Compatibility (EMC)** CFR 47 Part 15, Subpart B, Class B | EN 55022, Class B | ICES-003 Issue 4 CAN

# ATSBT-TOP-FM-5G | D85E01P86

/CSA-CEI/IEC CISPR 22:02

<b>Impedance</b>	50 ohm
<b>Interface Protocol Signal</b>	Data   dc
<b>Lightning Surge Capability</b>	5 times @ -3 kA   5 times @ 3 kA
<b>Lightning Surge Capability Test Method</b>	IEC 61000-4-5, Level X
<b>Lightning Surge Capability Waveform</b>	1.2/50 voltage and 8/20 current combination waveform
<b>Operating Frequency Band</b>	600 – 4200 MHz
<b>Power Consumption, maximum</b>	0.6 W
<b>Protocol</b>	AISG 1.1   AISG 2.0
<b>RF Power, maximum</b>	500 W (CW Tone)
<b>Voltage Range</b>	10–30 Vdc
<b>VSWR   Return Loss</b>	1.09:1   27 dB, typical

## Material Specifications

<b>Material Type</b>	Aluminum
----------------------	----------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67

## Packaging and Weights

<b>Weight, net</b>	0.9 kg   1.984 lb
--------------------	-------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

