

LS2-XMPHMP-3M-P-W



LSF2-50 SureFlex® Jumper with interface types NEX10 Push-Pull Male and 4.3-10 Push-Pull Male with HELIAX® SureGuard weatherproofing, 3M

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® Premium, static PIM
Product Brand	HELIAX® SureFlex® SureGuard®
Product Series	LSF2-50

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Push pull
Body Style, Connector B	Push pull
Interface, Connector A	NEX10 Male
Interface, Connector B	4.3-10 Male

Dimensions

Length	3 m 9.843 ft
Nominal Size	3/8 in

Logo Image

LS2-XMPHMP-3M-P-W



Electrical Specifications

3rd Order IMD Static	-119 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–970 MHz	1.065	30
1700–2200 MHz	1.083	28
2200–2700 MHz	1.106	26
3400–3800 MHz	1.222	20
3800–6000 MHz	1.288	18

Jumper Assembly Sample Label

LS2-XMPHMP-3M-P-W



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX[®] SureGuard weatherproofing boot