## HCA-AOIA



# Fiber Optic Drop Cable Assembly, PRODIGY™ Connector Core to Stub, SST Dielectric Cable

- Cable assembly with the Prodigy<sup>™</sup> small form hardened connector
- Compact and small footprint, space-saving design for high-density environments
- Compatible with multiple hardened connectors

#### Product Classification


Regional Availability	North America
Product Type	Fiber drop cable assembly
Product Brand	PRODIGY™
Product Series	HCA
General Specifications	
Cable Type	Dielectric - Flat
Connector A, quantity	1
Color, boot A	Black
Color, connector A	Black
Interface, Connector A	Prodigy
Interface, Connector B	Unterminated
Jacket Color	Black
Total Fibers, quantity	1
Dimensions	
Cable Assembly Length Range (ft)	1 – 2000
Cable Outer Diameter	4.5 x 8.0 mm (0.18 x 0.31 in)

### Outline Drawing

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 10, 2024








#### Ordering Tree

#### Prodigy Hardened Cable Assembly



Cable length shown as an example; additional cable lengths available upon request up to 2,000 ft (600 m)

\*\* Cable K type lengths only available up to 1,300 ft (400 m) \*\*\* Cable V and X types available in lengths up to 2,000 ft (600 m)

#### Mechanical Specifications

Minimum Bend Radius, loaded	90 mm   3.543 in
Minimum Bend Radius, unloaded	81 mm   3.189 in

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 10, 2024

**COMMSCOPE**<sup>®</sup>

## ΗCA-AOIA

Tensile Load, long term, maximum	400 N   89.924 lbf
Tensile Load, short term, maximum	1334 N   299.895 lbf
Cable Crush Resistance, maximum	10 N/mm   57.101 lb/in
Dust Cap Pulling Force, minimum	445 N   100.04 lbf
Mating Durability, maximum	0.5 dB @ 100 cycles

#### **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	G.657.A2/B2
Insertion Loss, maximum, connector A	0.4 dB
Insertion Loss, typical	0.15 dB
Return Loss, minimum, connector A	65 dB

#### **Environmental Specifications**

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Outdoor
Jacket UV Resistance	UV stabilized
Qualification Standards	Telcordia GR-3120-CORE

#### Packaging and Weights

Cable weight

39 kg/km | 26.207 lb/kft

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 10, 2024

