

# L1-PNMNM-50

---

LDF1-50 Jumper with interface types N Male and N Male, 15.24 m



## Product Classification

<b>Product Type</b>	SureFlex® standard
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	LDF1-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	N Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	15.24 m   50 ft
<b>Nominal Size</b>	1/4 in

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>700–3000 MHz</b>	1.43	15.05

## Jumper Assembly Sample Label

# L1-PNMNM-50



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

- 35422-50 – Heat Treated LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket
- LDF1-50 – LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket
- LDF1-50-43 – LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

# 35422-50

---

Heat Treated LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket



## Product Classification

<b>Product Type</b>	Coaxial wireless cable
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	LDF1-50

## General Specifications

<b>Flexibility</b>	Standard
<b>Jacket Color</b>	Black
<b>Performance Note</b>	Attenuation values typical, guaranteed within 5%

## Dimensions

<b>Diameter Over Dielectric</b>	6.858 mm   0.27 in
<b>Diameter Over Jacket</b>	8.763 mm   0.345 in
<b>Inner Conductor OD</b>	2.54 mm   0.1 in
<b>Outer Conductor OD</b>	7.874 mm   0.31 in
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>Cable Impedance</b>	50 ohm ±1 ohm
<b>Capacitance</b>	76.8 pF/m   23.409 pF/ft
<b>dc Resistance, Inner Conductor</b>	5.151 ohms/km   1.57 ohms/kft
<b>dc Resistance, Outer Conductor</b>	4.003 ohms/km   1.22 ohms/kft
<b>dc Test Voltage</b>	2200 V
<b>Inductance</b>	0.194 µH/m   0.059 µH/ft
<b>Insulation Resistance</b>	100000 MOhms-km

# 35422-50

<b>Jacket Spark Test Voltage (rms)</b>	5000 V
<b>Operating Frequency Band</b>	1 – 15800 MHz
<b>Peak Power</b>	12.1 kW
<b>Velocity</b>	86 %

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>806–960 MHz</b>	1.15	23.13
<b>1700–2000 MHz</b>	1.15	23.13

## Attenuation

<b>Frequency (MHz)</b>	<b>Attenuation (dB/100 m)</b>	<b>Attenuation (dB/100 ft)</b>	<b>Average Power (kW)</b>
<b>1.0</b>	0.394	0.12	12.1
<b>1.5</b>	0.483	0.147	12.1
<b>2.0</b>	0.558	0.17	12.1
<b>10.0</b>	1.254	0.382	5.83
<b>20.0</b>	1.781	0.543	4.11
<b>30.0</b>	2.188	0.667	3.34
<b>50.0</b>	2.838	0.865	2.58
<b>85.0</b>	3.724	1.135	1.96
<b>88.0</b>	3.791	1.156	1.93
<b>100.0</b>	4.049	1.234	1.81
<b>108.0</b>	4.213	1.284	1.74
<b>150.0</b>	4.993	1.522	1.47
<b>174.0</b>	5.392	1.644	1.36
<b>200.0</b>	5.798	1.767	1.26
<b>204.0</b>	5.858	1.785	1.25
<b>300.0</b>	7.168	2.185	1.02
<b>400.0</b>	8.342	2.543	0.88
<b>450.0</b>	8.88	2.706	0.82
<b>460.0</b>	8.984	2.738	0.81
<b>500.0</b>	9.391	2.862	0.78
<b>512.0</b>	9.511	2.899	0.77
<b>600.0</b>	10.351	3.155	0.71
<b>700.0</b>	11.244	3.427	0.65

# 35422-50

---

<b>800.0</b>	12.084	3.683	0.61
<b>824.0</b>	12.278	3.742	0.6
<b>894.0</b>	12.833	3.911	0.57
<b>960.0</b>	13.339	4.066	0.55
<b>1000.0</b>	13.639	4.157	0.54
<b>1218.0</b>	15.192	4.63	0.48
<b>1250.0</b>	15.41	4.697	0.47
<b>1500.0</b>	17.04	5.194	0.43
<b>1700.0</b>	18.266	5.567	0.4
<b>1794.0</b>	18.823	5.737	0.39
<b>1800.0</b>	18.858	5.748	0.39
<b>2000.0</b>	20.003	6.097	0.37
<b>2100.0</b>	20.559	6.266	0.36
<b>2200.0</b>	21.104	6.432	0.35
<b>2300.0</b>	21.64	6.596	0.34
<b>2500.0</b>	22.686	6.914	0.32
<b>2700.0</b>	23.701	7.224	0.31
<b>3000.0</b>	25.171	7.672	0.29
<b>3400.0</b>	27.048	8.244	0.27
<b>3600.0</b>	27.956	8.521	0.26
<b>3700.0</b>	28.403	8.657	0.26
<b>3800.0</b>	28.846	8.792	0.25
<b>3900.0</b>	29.284	8.925	0.25
<b>4000.0</b>	29.719	9.058	0.25
<b>4100.0</b>	30.149	9.189	0.24
<b>4200.0</b>	30.576	9.319	0.24
<b>4300.0</b>	30.999	9.448	0.24
<b>4400.0</b>	31.419	9.576	0.23
<b>4500.0</b>	31.835	9.703	0.23
<b>4600.0</b>	32.249	9.829	0.23
<b>4700.0</b>	32.659	9.954	0.22
<b>4800.0</b>	33.066	10.078	0.22
<b>4900.0</b>	33.47	10.201	0.22
<b>5000.0</b>	33.871	10.323	0.22
<b>6000.0</b>	37.742	11.503	0.19

# 35422-50

---

<b>8000.0</b>	44.888	13.681	0.16
<b>8800.0</b>	47.579	14.501	0.15
<b>10000.0</b>	51.475	15.689	0.14
<b>12000.0</b>	57.664	17.575	0.13
<b>14000.0</b>	63.552	19.37	0.12
<b>15800.0</b>	68.646	20.922	0.11

## Material Specifications

<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	PE
<b>Inner Conductor Material</b>	Copper-clad aluminum wire
<b>Outer Conductor Material</b>	Corrugated copper

## Mechanical Specifications

<b>Minimum Bend Radius, multiple Bends</b>	76.2 mm   3 in
<b>Minimum Bend Radius, single Bend</b>	38.1 mm   1.5 in
<b>Number of Bends, minimum</b>	15
<b>Number of Bends, typical</b>	30
<b>Tensile Strength</b>	91 kg   200.62 lb
<b>Bending Moment</b>	1.4 N-m   12.391 in lb
<b>Flat Plate Crush Strength</b>	1.4 kg/mm   78.396 lb/in

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C

## Packaging and Weights

<b>Cable weight</b>	0.09 kg/m   0.06 lb/ft
---------------------	------------------------

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

# LDF1-50

---

LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket



## Product Classification

<b>Product Type</b>	Coaxial wireless cable
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	LDF1-50   MLOC

## General Specifications

<b>Product Number</b>	520100002/00   SZ520100002/00
<b>Flexibility</b>	Standard
<b>Jacket Color</b>	Black
<b>Performance Note</b>	Attenuation values typical, guaranteed within 5%

## Dimensions

<b>Diameter Over Dielectric</b>	6.858 mm   0.27 in
<b>Diameter Over Jacket</b>	8.763 mm   0.345 in
<b>Inner Conductor OD</b>	2.54 mm   0.1 in
<b>Outer Conductor OD</b>	7.874 mm   0.31 in
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>Cable Impedance</b>	50 ohm $\pm$ 1 ohm
<b>Capacitance</b>	76.8 pF/m   23.409 pF/ft
<b>dc Resistance, Inner Conductor</b>	5.151 ohms/km   1.57 ohms/kft
<b>dc Resistance, Outer Conductor</b>	4.003 ohms/km   1.22 ohms/kft
<b>dc Test Voltage</b>	2200 V
<b>Inductance</b>	0.194 $\mu$ H/m   0.059 $\mu$ H/ft



# LDF1-50

<b>Insulation Resistance</b>	100000 MOhms-km
<b>Jacket Spark Test Voltage (rms)</b>	5000 V
<b>Operating Frequency Band</b>	1 – 15800 MHz
<b>Peak Power</b>	12.1 kW
<b>Velocity</b>	86 %

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>	<b>VSWR, typical</b>	<b>Return Loss, typical (dB)</b>
<b>806–960 MHz</b>	1.15	23.13		
<b>1700–2000 MHz</b>	1.15	23.13		
<b>4000–6000 MHz</b>	1.433	14.99	1.29	18

## Attenuation

<b>Frequency (MHz)</b>	<b>Attenuation (dB/100 m)</b>	<b>Attenuation (dB/100 ft)</b>	<b>Average Power (kW)</b>
<b>1.0</b>	0.394	0.12	12.1
<b>1.5</b>	0.483	0.147	12.1
<b>2.0</b>	0.558	0.17	12.1
<b>10.0</b>	1.254	0.382	5.83
<b>20.0</b>	1.781	0.543	4.11
<b>30.0</b>	2.188	0.667	3.34
<b>50.0</b>	2.838	0.865	2.58
<b>85.0</b>	3.724	1.135	1.96
<b>88.0</b>	3.791	1.156	1.93
<b>100.0</b>	4.049	1.234	1.81
<b>108.0</b>	4.213	1.284	1.74
<b>150.0</b>	4.993	1.522	1.47
<b>174.0</b>	5.392	1.644	1.36
<b>200.0</b>	5.798	1.767	1.26
<b>204.0</b>	5.858	1.785	1.25
<b>300.0</b>	7.168	2.185	1.02
<b>400.0</b>	8.342	2.543	0.88
<b>450.0</b>	8.88	2.706	0.82
<b>460.0</b>	8.984	2.738	0.81
<b>500.0</b>	9.391	2.862	0.78
<b>512.0</b>	9.511	2.899	0.77

# LDF1-50

---

<b>600.0</b>	10.351	3.155	0.71
<b>700.0</b>	11.244	3.427	0.65
<b>800.0</b>	12.084	3.683	0.61
<b>824.0</b>	12.278	3.742	0.6
<b>894.0</b>	12.833	3.911	0.57
<b>960.0</b>	13.339	4.066	0.55
<b>1000.0</b>	13.639	4.157	0.54
<b>1218.0</b>	15.192	4.63	0.48
<b>1250.0</b>	15.41	4.697	0.47
<b>1500.0</b>	17.04	5.194	0.43
<b>1700.0</b>	18.266	5.567	0.4
<b>1794.0</b>	18.823	5.737	0.39
<b>1800.0</b>	18.858	5.748	0.39
<b>2000.0</b>	20.003	6.097	0.37
<b>2100.0</b>	20.559	6.266	0.36
<b>2200.0</b>	21.104	6.432	0.35
<b>2300.0</b>	21.64	6.596	0.34
<b>2500.0</b>	22.686	6.914	0.32
<b>2700.0</b>	23.701	7.224	0.31
<b>3000.0</b>	25.171	7.672	0.29
<b>3400.0</b>	27.048	8.244	0.27
<b>3600.0</b>	27.956	8.521	0.26
<b>3700.0</b>	28.403	8.657	0.26
<b>3800.0</b>	28.846	8.792	0.25
<b>3900.0</b>	29.284	8.925	0.25
<b>4000.0</b>	29.719	9.058	0.25
<b>4100.0</b>	30.149	9.189	0.24
<b>4200.0</b>	30.576	9.319	0.24
<b>4300.0</b>	30.999	9.448	0.24
<b>4400.0</b>	31.419	9.576	0.23
<b>4500.0</b>	31.835	9.703	0.23
<b>4600.0</b>	32.249	9.829	0.23
<b>4700.0</b>	32.659	9.954	0.22
<b>4800.0</b>	33.066	10.078	0.22
<b>4900.0</b>	33.47	10.201	0.22

# LDF1-50

---

5000.0	33.871	10.323	0.22
6000.0	37.742	11.503	0.19
8000.0	44.888	13.681	0.16
8800.0	47.579	14.501	0.15
10000.0	51.475	15.689	0.14
12000.0	57.664	17.575	0.13
14000.0	63.552	19.37	0.12
15800.0	68.646	20.922	0.11

## Material Specifications

<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	PE
<b>Inner Conductor Material</b>	Copper-clad aluminum wire
<b>Outer Conductor Material</b>	Corrugated copper

## Mechanical Specifications

<b>Minimum Bend Radius, multiple Bends</b>	76.2 mm   3 in
<b>Minimum Bend Radius, single Bend</b>	38.1 mm   1.5 in
<b>Number of Bends, minimum</b>	15
<b>Number of Bends, typical</b>	30
<b>Tensile Strength</b>	91 kg   200.62 lb
<b>Bending Moment</b>	1.4 N-m   12.391 in lb
<b>Flat Plate Crush Strength</b>	1.4 kg/mm   78.396 lb/in

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C

## Packaging and Weights

<b>Cable weight</b>	0.09 kg/m   0.06 lb/ft
---------------------	------------------------

# LDF1-50

---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# LDF1-50-43

---

LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket



## Product Classification

<b>Product Type</b>	Coaxial wireless cable
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	LDF1-50

## General Specifications

<b>Flexibility</b>	Standard
<b>Jacket Color</b>	Black
<b>Performance Note</b>	Attenuation values typical, guaranteed within 5%

## Dimensions

<b>Diameter Over Dielectric</b>	6.858 mm   0.27 in
<b>Diameter Over Jacket</b>	8.763 mm   0.345 in
<b>Inner Conductor OD</b>	2.54 mm   0.1 in
<b>Outer Conductor OD</b>	7.874 mm   0.31 in
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>Cable Impedance</b>	50 ohm ±1 ohm
<b>Capacitance</b>	76.8 pF/m   23.409 pF/ft
<b>dc Resistance, Inner Conductor</b>	5.151 ohms/km   1.57 ohms/kft
<b>dc Resistance, Outer Conductor</b>	4.003 ohms/km   1.22 ohms/kft
<b>dc Test Voltage</b>	3000 V
<b>Inductance</b>	0.194 µH/m   0.059 µH/ft
<b>Insulation Resistance</b>	100000 MOhms-km

# LDF1-50-43

<b>Jacket Spark Test Voltage (rms)</b>	5000 V
<b>Operating Frequency Band</b>	1 – 15800 MHz
<b>Peak Power</b>	12.1 kW
<b>Velocity</b>	86 %

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>100–400 MHz</b>	1.17	22.13
<b>680–960 MHz</b>	1.2	20.83
<b>1700–2200 MHz</b>	1.2	20.83

## Attenuation

<b>Frequency (MHz)</b>	<b>Attenuation (dB/100 m)</b>	<b>Attenuation (dB/100 ft)</b>	<b>Average Power (kW)</b>
<b>1.0</b>	0.394	0.12	12.1
<b>1.5</b>	0.483	0.147	12.1
<b>2.0</b>	0.558	0.17	12.1
<b>10.0</b>	1.254	0.382	5.83
<b>20.0</b>	1.781	0.543	4.11
<b>30.0</b>	2.188	0.667	3.34
<b>50.0</b>	2.838	0.865	2.58
<b>85.0</b>	3.724	1.135	1.96
<b>88.0</b>	3.791	1.156	1.93
<b>100.0</b>	4.049	1.234	1.81
<b>108.0</b>	4.213	1.284	1.74
<b>150.0</b>	4.993	1.522	1.47
<b>174.0</b>	5.392	1.644	1.36
<b>200.0</b>	5.798	1.767	1.26
<b>204.0</b>	5.858	1.785	1.25
<b>300.0</b>	7.168	2.185	1.02
<b>400.0</b>	8.342	2.543	0.88
<b>450.0</b>	8.88	2.706	0.82
<b>460.0</b>	8.984	2.738	0.81
<b>500.0</b>	9.391	2.862	0.78
<b>512.0</b>	9.511	2.899	0.77
<b>600.0</b>	10.351	3.155	0.71

# LDF1-50-43

---

<b>700.0</b>	11.244	3.427	0.65
<b>800.0</b>	12.084	3.683	0.61
<b>824.0</b>	12.278	3.742	0.6
<b>894.0</b>	12.833	3.911	0.57
<b>960.0</b>	13.339	4.066	0.55
<b>1000.0</b>	13.639	4.157	0.54
<b>1218.0</b>	15.192	4.63	0.48
<b>1250.0</b>	15.41	4.697	0.47
<b>1500.0</b>	17.04	5.194	0.43
<b>1700.0</b>	18.266	5.567	0.4
<b>1794.0</b>	18.823	5.737	0.39
<b>1800.0</b>	18.858	5.748	0.39
<b>2000.0</b>	20.003	6.097	0.37
<b>2100.0</b>	20.559	6.266	0.36
<b>2200.0</b>	21.104	6.432	0.35
<b>2300.0</b>	21.64	6.596	0.34
<b>2500.0</b>	22.686	6.914	0.32
<b>2700.0</b>	23.701	7.224	0.31
<b>3000.0</b>	25.171	7.672	0.29
<b>3400.0</b>	27.048	8.244	0.27
<b>3600.0</b>	27.956	8.521	0.26
<b>3700.0</b>	28.403	8.657	0.26
<b>3800.0</b>	28.846	8.792	0.25
<b>3900.0</b>	29.284	8.925	0.25
<b>4000.0</b>	29.719	9.058	0.25
<b>4100.0</b>	30.149	9.189	0.24
<b>4200.0</b>	30.576	9.319	0.24
<b>4300.0</b>	30.999	9.448	0.24
<b>4400.0</b>	31.419	9.576	0.23
<b>4500.0</b>	31.835	9.703	0.23
<b>4600.0</b>	32.249	9.829	0.23
<b>4700.0</b>	32.659	9.954	0.22
<b>4800.0</b>	33.066	10.078	0.22
<b>4900.0</b>	33.47	10.201	0.22
<b>5000.0</b>	33.871	10.323	0.22

# LDF1-50-43

---

<b>6000.0</b>	37.742	11.503	0.19
<b>8000.0</b>	44.888	13.681	0.16
<b>8800.0</b>	47.579	14.501	0.15
<b>10000.0</b>	51.475	15.689	0.14
<b>12000.0</b>	57.664	17.575	0.13
<b>14000.0</b>	63.552	19.37	0.12
<b>15800.0</b>	68.646	20.922	0.11

## Material Specifications

<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	PE
<b>Inner Conductor Material</b>	Copper-clad aluminum wire
<b>Outer Conductor Material</b>	Corrugated copper

## Mechanical Specifications

<b>Minimum Bend Radius, multiple Bends</b>	76.2 mm   3 in
<b>Minimum Bend Radius, single Bend</b>	38.1 mm   1.5 in
<b>Number of Bends, minimum</b>	15
<b>Number of Bends, typical</b>	30
<b>Tensile Strength</b>	91 kg   200.62 lb
<b>Bending Moment</b>	1.4 N-m   12.391 in lb
<b>Flat Plate Crush Strength</b>	1.4 kg/mm   78.396 lb/in

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C

## Packaging and Weights

<b>Cable weight</b>	0.09 kg/m   0.06 lb/ft
---------------------	------------------------



# LDF1-50-43

---

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system